

DR. JOHANNES HEIDENHAIN GmbH
 Dr.-Johannes-Heidenhain-Straße 5
 83301 Traunreut, Germany
 ☎ +49 (8669) 31-0
 📠 +49 (8669) 5061
 E-Mail: info@heidenhain.de


Technical support 📠 +49 (8669) 32-1000
Measuring systems ☎ +49 (8669) 31-3104
 E-Mail: service.ms-support@heidenhain.de
TNC support ☎ +49 (8669) 31-3101
 E-Mail: service.nc-support@heidenhain.de
NC programming ☎ +49 (8669) 31-3103
 E-Mail: service.nc-pgm@heidenhain.de
PLC programming ☎ +49 (8669) 31-3102
 E-Mail: service.plc@heidenhain.de
Lathe controls ☎ +49 (8669) 31-3105
 E-Mail: service.lathe-support@heidenhain.de

www.heidenhain.de



MT 1271


mm
 Tolerancing ISO 8015
 ISO 2768 - m H
 < 6 mm: ±0.2 mm





Ⓡ = Referenzmarken-Lage
 Reference mark position
 marque de référence
 indici di riferimento
 marca de referencia

Ⓢ = Beginn der Messlänge ML
 Begin. of meas. length ML
 début longueur utile ML
 inizio lunghezza di misura ML
 comienzo longitud útil ML

Ø 4.5 mm	$R_1 \geq 10 \text{ mm}$	$R_2 \geq 50 \text{ mm}$
	$R_1 \geq 40 \text{ mm}$	$R_2 \geq 100 \text{ mm}$



	°C (°F)	
		10 ... 40 °C (50 ... 104 °F)
		-20 ... 70 °C (-4 ... 158 °F)



Abtastfrequenz
Scanning frequency
fréquence de balayage
frequenza di scansione
frecuencia de captacion

kHz	v max. [m/min]	
	TTL x 5	TTL x 10
25	-	3
50	6	6
100	12	12
200	24	-

